

Hei-VAC Valve Control Technical datasheet



Dimensions (W × H × D)	196 x 243 x 309 mm
Weight	12 kg
Protection class (EN 60529)	IP 40
Connection	n.a.
Operating temperature	+10 - +40°C
Motor protection	thermal cutout, manual reset
Storage temperature range	-10 - +60°C
Power	Electrical: 0,18 kW
Maximum pumping speed	2.0 / 2.3 m ³ /h
Ultimate vacuum (absolute)	without gas ballast: 7 mbar with gas ballast: 12 mbar
Maximum permissible pressure	1.1 bar
Permissible relative atmospheric moisture during operation (no condensation)	30% - 85%
Maximum no-load speed	1500 / 1800 min ⁻¹
Inlet	hose nozzle DN 8 mm
Outlet	hose nozzle DN 8 mm
Maximum permissible range of supply voltage (±10%)	100-115 V~ 50/60 Hz, 120V~ 60 Hz, 230 V~ 50/60 Hz