



designed for scientists



S 18 N - 10 G Dispersing tool

/// Data Sheet

Suitable for dispersing instrument T 18 digital

Working range: 1 - 100 ml

Stator diameter: 10 mm

Immersion depth: 25 - 70 mm

Materials in contact with medium: PTFE, AISI 316L

Suitable for solvents

Max. temperature: 180 °C

Sterilization methods: all methods



designed for scientists

Technical Data

Volume range (H ₂ O) [l]	0.001 - 0.1
Stator diameter [mm]	10
Rotor diameter [mm]	7.5
Gap between rotor and stator [mm]	0.35
allowable Speed max. [rpm]	25000
Circumferential speed max. [m/s]	9.8
Immersion depth [mm]	25 - 70
Shaft length [mm]	108
Material in contact with medium	PTFE, AISI 316L
pH range	2 - 13
Suitable for solvents	yes
Suitable for abrasive substances	yes
Working temperature max. [°C]	180
Sterilization methods	all methods
Ultimate fineness, suspensions [µm]	10 - 50
Ultimate fineness, emulsions [µm]	1 - 10
Weight [kg]	0.094
Permissible ambient temperature [°C]	5 - 40