



designed for scientists



S 25 D - 14 G - KS Dispersing tool (12 Pc)

/// Data Sheet

Suitable for dispersing instrument T 25 digital

Working range: 10 - 500 ml

Stator diameter: 14 mm

Immersion depth: 15 - 85 mm

Materials in contact with medium: Polycarbonate (PC), Polyetheretherketon (PEEK)

Max. temperature: 100 °C

Sterilization methods: autoclavable

Plastic materials used approved by FDA.

Packaging unit: 12 pieces



designed for scientists

Technical Data

Volume range (H ₂ O) [l]	0.01 - 0.5
Stator diameter [mm]	14
Rotor diameter [mm]	9.5
Circumferential speed max. [m/s]	12
Immersion depth [mm]	15 - 85
Shaft length [mm]	150
Material in contact with medium	Polycarbonat (PC), Polyetheretherketon (PEEK)
Working temperature max. [°C]	100
Sterilization methods	autoclavable
Weight [kg]	0.222
Permissible ambient temperature [°C]	5 - 40