



## Perfect for Routine Moisture Testing

The new OHAUS MB32 features a redesigned housing with stronger material, innovative carbon fiber heating technology and an upgraded load cell for enhanced durability and performance. The easy-to-use MB32 is the perfect choice for routine moisture testing.

### Unique Features:

- An LCD with second line display, navigation knob, and intuitive operation system makes for convenient routine moisture testing.
- The new carbon fiber heating technology and upgraded loadcell shortens analysis time, saves power and keeps results accurate and consistent.
- Robust, slim design with a strong housing ensures MB32's durability even in harsh environments.



## Do more with OHAUS

Check out the OHAUS laboratory equipment portfolio!  
[www.ohaus.com](http://www.ohaus.com)

# MB32 Moisture Analyzers

## Specifications

Model	MB32
Readability	0,01 % / 0,001 g
Repeatability	0,15 % (3 g sample) 0,02 % (10 g sample)
Moisture Range	0,01 % to 100 % (0,01 % to 1000 % in regain mode)
Recommended MC%	0,5 % to 100 %
Minimum Start Weight	0,5 g
Capacity	90 g
Heating Element	Carbon Fiber
Temperature Range	40 – 180°C (1°C incremental)
Drying Programs	Standard, Fast
Method Library	2
Result Storage	1
Switch-off Criteria	3 automatic, timed (1 – 480 mins), manual
ID Management	–
Status Light	–
Operation Instruction	Progress indicator On-screen instruction
Display Type	4" LCD with 2 <sup>nd</sup> line display
Display Results	MC%, DC%, RG%, time, temperature, weight, Method No.
Language	English, French, German, Italian, Spanish, Portuguese, Chinese, Korean, Japanese, Polish, Turkish
Adjustment	Temperature adjustment (100°C, 160°C) External weight adjustment (50 g)
Output	RS232, USB device
Power	120 or 240 VAC 50/60 Hz
Operating Temperature Range	10 – 40°C
Pan Size	Ø 90 mm
Dimensions	210×138×352 mm
Net Weight	4,3 kg
Shipping Weight	6,1 kg


## Compliance

- **Product Safety:** IEC/EN 61010-1; IEC/EN 61010-2-010; CAN/CSA C22.2 61010-1; CAN/CSA C22.2 61010-2-010; UL 61010-1; UL 61010-2-010
- **Electromagnetic Compatibility:** IEC/EN 61326-1 Class B, Basic environments; FCC Part 15 Class A; Canada ICES-003 Class A
- **Compliance Marks:** CSA; CE; RCM; WEEE

## Accessories

Pan Handler, MB32 MB62 MB92 .....	30954234
In-Use Cover, MB32 MB62 .....	30954235
Temperature Calibration Kit .....	11113857
Scoop .....	30284477
Aluminum Pan (50) .....	30585411
Glass Fiber Pads (200) .....	80850087
Cage, Sample .....	80252477
Reusable Pan, Set (3), 7mm .....	80252478
Reusable Pan, Set (3), 14mm .....	80252479
SF40A Impact Printer .....	30064202

## Outline Dimensions



80776947\_A 20240619 © Copyright OHAUS Corporation

**OHAUS Europe GmbH**

e-mail: [ssc@ohaus.com](mailto:ssc@ohaus.com)

Tel: 0041 22 567 53 19

e-mail: [tsc@ohaus.com](mailto:tsc@ohaus.com)

Tel: 0041 22 567 53 20

[www.ohaus.com](http://www.ohaus.com)

The management system governing the manufacture of this product is ISO 9001:2015 certified.

