

# Incubator | shaking

top door-type, up to 60°C / 10°C - 60°C (refrigerated), 30-250 rpm, orbital motion



Orbital motion



Wise remote



Jog-Shuttle controller

**IQ | OQ**  
available  
page 12 for details

## WIS-10 top door, 60°C, orbital

### Ideal for:

- biological cultures under various temperatures

### Features:


- CFC free refrigerant (R-404A)
- easy access to bench top by liftable door
- RS232C interface for monitoring and controlling (WireRemote)
- advanced shaking mechanism provides quiet shaking and precise speed control
- stabilized orbital motion, minimum noise and no vibration
- 60W krypton lamp (WIS-10RL)
- universal platform included
- accommodates flasks up to 1000 ml
- durable and flexible plastic flask holder (optional)
- universal spring rack for various flask shapes/sizes (optional)
- stainless steel interior and powder-coated body
- backlight LCD display
- CE certified and unique serial number for tracing

### Safety mechanism:

- overheat and over-current protection
- sensor error detection and leakage breaker
- automatic operation stop when door opens

### Controller:

- digital fuzzy controller with **Jog-Shuttle-switch** (turn + push)



WIS-10 with universal platform (included)

Model	WIS-10	WIS-10R	WIS-10RL
Temperature range	R/T +5°C - 60°C	+10°C - 60°C (refrigerated)	
Temperature accuracy & uniformity	accuracy: ±0.2°C at 37°C, uniformity: ±0.5°C at 37°C		
Temperature sensor	PT100 sensor		
Heater	800 W	1 kW	1.2 kW
Compressor	none	250 W	
Compressor control	none	refrigerator control for preventing overload	
Shaking speed & stroke	30 - 250 rpm, 25 mm orbital motion		
Timer & alarm	99hr 59 min (delay & continuous run), error status and timer end		
Room lamp	-	Krypton lamp, 60 W	
Max. capacity of flask holder 50-100 ml	68 pcs. flask holder for 50 - 100 ml flasks		
Max. capacity of flask holder 200-300 ml	36 pcs. flask holder for 200 - 300 ml flasks		
Max. capacity of flask holder 500 - 1000 ml	21 pcs. flask holder for 500 - 1000 ml flasks		
Internal dimensions (W x D x H)	750 x 720 x 400 mm		
External dimensions (W x D x H)	1065 x 900 x 980 mm		
Packing size & gross weight	1220 x 1060 x 1200 mm, 231 kg	1220 x 1060 x 1200 mm, 238 kg	1220 x 1060 x 1200 mm, 238 kg
Power supply	1 Phase AC 120V, 60 Hz or AC 230V, 50/60 Hz		
Power consumption	800 W	1,8 kW	2,1 kW
Order number 230V	DH.WIS00210	DH.WIS04210	DH.WIS05210
Order number 120V	DH.WIS00110	DH.WIS04110	DH.WIS05110

Accessories: Suitable platforms, racks and flask holder can be found on page 75