




Quick-display precision balance with user-friendly concept of operation modes – now with larger housing for more stability

Features

- **Easy to use:** All primary functions have their own key on the keypad
- **Compact size,** practical for small spaces
- **Capacity display:** A bar lights up to show how much of the weighing capacity is still available
- **Level indicator and levelling feet** for precise levelling of the scale, fitted as standard, to give the most accurate weighing result
- **Draught shield** standard for models with weighing plate size **A** and **B**, Weighing space W×D×H 158×143×64 mm

Technical data

- Backlit LCD display, digit height 15 mm
- Dimensions weighing surface, stainless steel
 - A** Ø 80 mm
 - B** Ø 120 mm
 - C** W×D 155×145 mm, see larger picture
- Overall dimensions W×D×H 210×315×90 mm (without draught shield)
- Net weight approx. 2,0 kg
- Permissible ambient temperature 15 °C/30 °C

Accessories

- **Protective working cover,** scope of delivery: 5 items, KERN PFB-A12S05, **€ 40,-**
- **1 Separate second display,** ideal for training and demonstration purposes in laboratories or industry, not permitted for direct sales to the public, KERN PFB-A08, **€ 115,-**
- **Bluetooth data interface** for wireless data transfer to PC or tablets, must be ordered at purchase
 - Bluetooth 2.0: KERN PFB-A10, **€ 95,-**
 - Bluetooth 4.0: KERN PFB-A11, **€ 125,-**
- Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION

FACTORY



PFB-A10 PFB-A11

Model	Weighing capacity [Max] g	Readability [d] g	Reproducibility g	Linearity g	Weighing plate	Price excl. of VAT ex works €	Option	
							DAkkS Calibr. Certificate	
KERN							DAkkS KERN	€
PFB 120-3	120	0,001	0,001	± 0,003	A	280,-	963-127	72,-
PFB 200-3	200	0,001	0,002	± 0,005	A	295,-	963-127	72,-
PFB 300-3	300	0,001	0,002	± 0,005	A	320,-	963-127	72,-
PFB 600-2	600	0,01	0,01	± 0,03	B	240,-	963-127	72,-
PFB 1200-2	1200	0,01	0,01	± 0,03	B	245,-	963-127	72,-
PFB 2000-2	2000	0,01	0,02	± 0,05	B	260,-	963-127	72,-
PFB 3000-2	3000	0,01	0,02	± 0,05	B	280,-	963-127	72,-
PFB 6000-1	6000	0,1	0,1	± 0,3	C	225,-	963-128	88,-
PFB 6000-2	6000	0,05	0,05	± 0,15	C	250,-	963-128	88,-