



designed for scientists



## MINISTAR 40 digital

/// Data Sheet

The space-saving high performers from IKA MICROSTAR and MINISTAR series have been complemented by additional models. The new and easy-to-use stirrers convince with perfect basic functionalities, as well as with a compact design.

Combining high performance with particular excellence, they require minimum space and come with a lifetime guarantee. See for yourself:

Compact design

The reduced design and the focus on the most essential aspects make the new IKA MICROSTAR and MINISTAR



designed for scientists

stirrers reliable laboratory companions.

#### Constant torque

All models of the IKA MICROSTAR and MINISTAR series guarantee a constant torque over the entire rpm range. The new devices are available in six different versions with rpms of up to 2,000 rpm and a torque of up to 80 Ncm.

#### Ease of operation

Operation takes place using a stable rotary knob. The display clearly shows the rotational speed.

#### Rapid updates

Regular software updates can be undertaken rapidly and simply via the USB interface.

## Technical Data

Stirring quantity max. per stirring position (H2O) [l]	25
Motor rating input [W]	60
Motor rating output [W]	46
Motor principle	Brushless DC
Speed display	LED
Speed min. [rpm]	50
Speed min. [rpm]	0/50
Speed max. [rpm]	1000
Viscosity max. [mPas]	30000
Output max. at stirring shaft [W]	42
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	40
Speed control	Turning knob
Setting accuracy speed [±rpm]	1
Deviation of speed measurement $n > 300\text{rpm}$ [±%]	1
Deviation of speed measurement $n < 300\text{rpm}$ [±rpm]	3
Stirring element fastening	chuck
Chuck range diameter [mm]	0.5 - 8
Hollow shaft, inner diameter [mm]	8.5
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	13
Extension arm length [mm]	160
Nominal torque [Nm]	0.4
Timer display	none
Housing material	alu-cast coating / thermoplastic polymer
Dimensions (W x H x D) [mm]	70 x 193 x 147
Weight [kg]	1.72
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 54
USB interface	yes
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	69
Power input standby [W]	0.5
DC Voltage [V=]	24
Current consumption [mA]	2900