



designed for scientists



HS 260 basic

/// Data Sheet

Compact, flat reciprocal shaker with ideal swivel motion, for a maximum shaking weight of 7.5 kg.

- Electronic adjustment of speed and timer
- LED display for speed and time adjustment
- Wide range of attachment combinations makes it possible to use almost all shapes and sizes of vessels
- Attachments are not included in delivery, please order separately



designed for scientists

Technical Data

Type of movement	reciprocating
Shaker diameter [mm]	20
Permissible shaking weight (incl. attachment) [kg]	7.5
Motor rating input [W]	45
Motor rating output [W]	10
Permissible ON time [%]	100
Speed min (adjustable) [rpm]	20
Speed range [rpm]	0 - 300
Speed display	LED line
Timer	yes
Timer display	LED line
Time setting range [min]	5 - 50
Operating mode	timer and continuous operation
Dimensions (W x H x D) [mm]	360 x 100 x 420
Weight [kg]	8.16
Permissible ambient temperature [°C]	5 - 50
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	220 - 240 / 100 - 120
Frequency [Hz]	50/60
Power input [W]	45

