

Overhead stirrer | Jar tester

Accessories: Stirring impellers and plate stands


Stirring impellers for high-torque overhead stirrer - Ø10mm

- universal-types and wide-range-types
- shaft made of stainless steel, blades made of stainless steel or PTFE-coated
- excellent resistance to acids, chemicals, corrosion and high temperatures


Type	Blades	Rod	Article	Order number
Propeller-type	3-bladed Ø60 x h15 mm	Ø10 x L500 mm	PL111	DH.WOS501111
Propeller-type	3-bladed Ø80 x h20 mm	Ø10 x L650 mm	PL112	DH.WOS501112
Propeller-type	3-bladed Ø100 x h24 mm	Ø10 x L800 mm	PL113	DH.WOS501113
Propeller-type	4-bladed Ø90 x h35 mm	Ø10 x L650 mm	PL116	DH.WOS501116
Propeller-type	4-bladed Ø110 x h40 mm	Ø10 x L800 mm	PL117	DH.WOS501117
Propeller-type	4-bladed Ø110 x h40 mm	Ø10 x L1000 mm	PL118	DH.WOS501118
Diamond-type	4-bladed Ø110 x h25 mm	Ø10 x L650 mm	PL121	DH.WOS501121
Centrifugal-type PTFE-coated	2-bladed Ø100 x h24 mm	Ø10 x L650 mm	PL130	DH.WOS501130
Anchor-type	2-bladed Ø90 x h16 mm	Ø10 x L650 mm	PL135	DH.WOS501135
Anchor-type	2-bladed Ø140 x h25 mm	Ø10 x L800 mm	PL136	DH.WOS501136
Anchor-type	2-bladed Ø160 x h30 mm	Ø10 x L1000 mm	PL137	DH.WOS501137




Propeller-type 3-bladed



Propeller-type 4-bladed



Diamond-type 4-bladed



Centrifugal-type PTFE-coated
2-bladed



Anchor-type 2-bladed