

## PRODUCT DATA SHEET



### VS 20 OH

With a slow rotation speed of 1 - 20 rpm, LAUDA Varioshake overhead shakers are ideal for shaking mixing and sedimentation cylinders, as well as bottles and tubes with viscous, pasty substances or powders.

Technical Attributes	VS 20 OH
Ambient temperature min.	10 °C
Ambient temperature max.	40 °C
Capacity	max. 12 bottles / jars; round or angular, up to max. 110 mm Ø and max. 270 mm height
Load capacity max.	20 kg
Shaking frequency min.	1 min <sup>-1</sup>
Shaking frequency max.	20 min <sup>-1</sup>
Shaking motion	overhead-rotating
Dimensions (WxDxH) in mm	770x700x715
Weight	62.0 kg

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Pfarrstraße 41/43 · 97922 Lauda-Königshofen  
Postfach 1251 · 97912 Lauda-Königshofen · DE

T +49 (0) 9343 503-0 · F +49 (0) 9343 503-222  
info@lauda.de · www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim · HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim · HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser