

Rotamax 120

P/N: 544-41200-00



The compact one with a maximum loading capacity of 2 kg

Space-saving and with a load weight of up to 2 kg, this shaker can perfectly master all applications.

The variably adjustable speed control (20-300 rpm) and the orbit of 20 mm guarantee homogeneous distribution. Your applications can be carried out in continuous operation or by means of a timer (max. 120 minutes).

Rotamax 120 - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	5.5 kg
Protection class IEC 60529	IP 30
Timer	yes (max. 120 min)
Rotation speed range	20 - 300 rpm
Power input	33 W
Dimensions (w/d/h)	245 x 310 x 125 mm
Max. Load	2 kg
Operating Mode	timer or continuous
Rotation speed setting	electronic control
Orbit / Stroke	20 mm
Platform size	220 x 220 mm
Accessories included	non-skid rubber mat
Angle	-
Motion	orbital