

KERN ADJ 100-4

KERN

The price leader in analytical balances with internal adjustment



Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0005 g
Maximum creep (15 minutes)	1 mg
Maximum creep (30 minutes)	2 mg

Approval	
CE mark	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	16 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	230×310×330 mm
Dimensions rectangular draught shield - inner (W×D×H)	170×160×205 mm
Dimensions rectangular draught shield - outer (W×D×H)	175×175×230 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	90 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Standby function	✓
Interfaces	RS-232 standard

Counting	
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	5, 10, 20, 50, 100
Counting resolution (laboratory conditions)	120.000

Power Supply	
Input voltage power supply / power [Max]	100 - 265 V; 50 - 60 Hz; 2,0 A

Category

Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ADJ

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	120 g
Weighing capacity [Max] (ct)	600 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,001 ct
Resolution	1.200.000
Linearity	± 0,0004 g
Reproducibility	0,0002 g
Tare range	120 g
Default unit	g

Units	g ct lb oz
-------	---------------------

USP Minimum weight of sample (k = 2, U = 0.1%)	400 mg
--	--------

Adjustment options	Internal calibration (automatic)
--------------------	----------------------------------

Recommended adjusting weight	120 g (E2)
------------------------------	------------

Possible calibration points	100 g; 120 g
-----------------------------	--------------

Automatic adjustment - Standard temperature deviation	2 °C
---	------

Automatic adjustment - Standard time interval	3 h
---	-----

Stabilization time	4 s
--------------------	-----

KERN ADJ 100-4

The price leader in analytical balances with internal adjustment

Input voltage device / power [Max]	12 V; 2 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH

Environmental conditions

Humidity of environment [Min]	20 %
Humidity of environment [Max]	85 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	375×524×412 mm
Net weight	5 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	16,2 kg

Services (optional)

Article number for DAkkS calibration	963-101
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

