

Cold light source compact single 20 W

HIGHLIGHTS

- Compact cold light source sources
- For Materials Science en Stereo microscopy
- Halogen 20 W version
- With \varnothing 6 mm fibre light conductor
- 2 years warranty

TECHNICAL SPECIFICATIONS

- Very compact and robust cold light source
- Supplied with a 40 cm self-sustaining \varnothing 6 mm glass fiber light conductor
- Equipped with a 20 W halogen lamp
- Light intensity is factory preset and can not be adjusted
- For 230 Volt operation

ILLUMINATION

Equipped with a 20 W halogen lamp. Light intensity is factory preset and can not be adjusted

MODEL

Power	20 W halogen
Color temperature	3,000 K
Operating voltage	110 V AC and 230 V AC versions (50/60 Hz)
Dimensions	(h) 80 x (w) 110 x (d) 165 mm
Weight	2.0 kg
Product Number	LE.5209



● LE.5209

