

Elmasonic Accessory - Elma Sink

Rinsing device

- for immersion rinsing or rinsing off objects
- Stainless steel tub
- Elma Sink L and XL are equipped with a drain
- the bath sizes are uniform to Elmasonic Easy, Select and P
- Product contents:
 - Elma Sink S & M: 1x Elma Sink S or M, 1x Operating and installation instructions
 - Elma Sink L & XL: 1x Elma Sink L or XL, 1x Embout de tuyau
1x Collier de serrage, 1x Operating and installation instructions



Unit size	S	M	L	XL
Order number	1113839	1113840	1113841	1113843
Tub size	40	60	180	300
passende Korbgröße				
20		2 x		
30	1 x			
40	1 x			
60		1 x	2 x	4 x
80			1 x	2 x
100				2 x
120			1 x	2 x
150				1 x
180			1 x	1 x
300				1 x

Elmasonic Accessory - Elma Sink

Rinsing device

Technical Data - Mechanics


Unit size	S		M	L			XL	
Total capacity V (l)	3,9		5,9	17,8			27,5	
Recom. operating capacity V _a (l)	2,9		4,3	14,2			22,0	
Unit ext. dimensions W / D / H (mm)	305 / 155 / 220		365 / 170 / 270	395 / 315 / 325			565 / 315 / 325	
Opening dimensions W ₂ / D ₂ (mm)	235 / 135		300 / 150	325 / 295			500 / 295	
Tank int. dimensions W ₁ / D ₁ / H ₁ (mm)	215 / 115 / 145		280 / 130 / 145	300 / 270 / 195			475 / 270 / 195	
Weight (kg)	2,0		2,8	4,7			6,1	
Connection thread drain (Zoll)	--			3/8				
Drain hose - ID (mm)	--			12				
Basket int. dimensions W ₃ / D ₃ / H ₃ (mm)	195 / 105 / 50	195 / 105 / 95	255 / 105 / 95	250 / 195 / 90	250 / 195 / 135	280 / 255 / 135	450 / 255 / 55	450 / 255 / 135
Total basket loading (kg)	1,0	3,0	5,0	6,0	7,0	8,0	7,0	10,0

Elmasonic Accessory - Elma Sink

Rinsing device


Dimension definition

Unit ext. dimensions




Tank int. dimensions

V_a : recommended operating capacity of the cleaning tank
(The actual operating capacity depends on the load.)



Basket int. dimensions



The drawings are meant as a visualization aid and are not true to scale.

Technical specifications serve as orientation values and are subject to tolerances due to production and manufacturing. Proper operation can only be guaranteed when using original Elma accessories.